

Accessories

Cooling Coils

For auxiliary cooling of circulators. The stainless steel coil, when connected to a water source, permits more rapid cool down from high temperatures or better control when operating close to ambient temperatures. Not recommended for use in circulator baths where fluid temperature exceeds the boiling point of water. For high temperature cool-down, we recommend Model 20, page 21.



For Heating Circulators Cat. No. 060300

For Model 72 and 7306 Cat. No. 050300

Digital-to-Analog Adapter

For circulators with Programmable Controller when direct digital control is not required. Connects to the RS232 port and provides 10mv/degree analog signal for external monitoring or control.

Cat. No. 060120

Glass Thermometer (non-mercury)

-20° to 150°C, 1°C **Cat. No. 099590**

Remote Probe

For circulators with Programmable Controller. Permits point of control to be switched from inside programmable circulator bath to a remote location, such as an open tank. Compensates for heat loss through tubing between the circulator and the control point. Platinum RTD sensor with stainless steel sheath $\frac{3}{16}$ dia. x 6 in. long (.47 dia. x 15.2 cm). One inch (2.54 cm) rubber coupling connects sheath to flexible cable. Probe cable ends in DB9 female plug.



10 ft. (3 m) Cat. No. 060101

25 ft. (7.6m) Cat. No. 060105

50 ft. (15.25m) Cat. No. 060110

Custom lengths available on special order.

Hollow Plastic Floating Balls

Create a blanket of insulation in any open bath, reducing heat loss 75% and evaporation by 87%. Also reduces fumes and splashing hazards. Usable to temperatures to 110°C and in most bath fluids. Made of polypropylene.



$\frac{3}{4}$ in. (20 mm) diameter,

Pack of 400 Cat. No. 060301

Tubing and Tubing Accessories

High-Temperature Tubing

3 ft. (.93m) flexible Teflon® lined, stainless steel over-braid tubing with $\frac{1}{8}$ in. NPT quick-connects at both ends. Maximum temperature 300°C.

3 ft. (.93m) Cat. No. 060310

Low-Temperature Insulated Tubing

Minimizes temperature loss from a circulator to external device. 6 ft. (1.9 m) of $\frac{1}{2}$ in. (1.27 cm) ID Buna N tubing with foam insulation.

6 ft. (1.9m) Cat. No. 060312

Tubing Clamp

3 mm to 13 mm tubing **Cat. No. 060304**

Brass Reducing Adapters

8 mm ID (Set of 2) **Cat. No. 060305**

3 mm (Set of 2) **Cat. No. 060306**

Buna N Tubing

8 mm ID per yard (.9m) **Cat No. 060307**

13 mm ID per yard (.9m) **Cat No. 060308**

Insulation

8 mm tubing per yard (.9m) **Cat. No. 060309**

13 mm tubing per yard (.9m) **Cat. No. 060311**